



PRT00270 – 2ft Plenum Rated Test Switch Cable Extender



Model #: PRT00270


12NC: 913702494101

Optional two-foot extension cable for newer metal 4-wire test switches

Specifications:


- This item includes one piece - a two-foot, plenum rated test switch cable consisting of a four-wire, plenum rated cable terminated in a male and female connector (see drawing at right for details).
- Item is packaged as shown in the drawing.
- The cable extender is designed to be used with Bodine Models BSL06M5, BSL14B2, BSL14B6, BSL20B2 and BSL20B6 along with the test switch cable assemblies provided with each of these products. Check compatibility with other products by contacting the factory at bodinetech@signify.com.
- As with other accessories, refer to the actual product installation instructions for more details.

Drawing:



NOTE:

1. ALL MATERIALS MUST BE RoHS COMPLIANT.
2. 100% OPEN AND SHORT ELECTRICAL TEST.
3. TESTING CONDITIONS:
VOLTAGE: 300V DC.
INSULATION RESISTANCE: 10 Mohms min.
CONDUCTIVE RESISTANCE: 2 Ohms max.



ITEM	PART NAME	DESCRIPTION	QTY
1	CABLE	22AWG*4C(RED,WHITE,GREEN,BLACK) PVC JACKET WHITE OD:3.6mm	AR
2	HOUSING	4PIN 2.54 HOUSING	1PCS
3	TERMINAL	2.54 TERMINAL	4PCS
4	HOUSING	PITCH 2.54 HOUSING	1PCS
5	TERMINAL	2.54 TERMINAL	4PCS
6	H/STUBE	H/S TUBE OD:4.0 BLACK	AR
7	P/BAG	PE BAG 80*200MM	1PCS

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. This product is designed for use with other Bodine branded products.